



## **PULLEY ON ROD – for use with a bench clamp**

**Cat: MF2600-001 Pulley on rod. Use with bench clamp**

### **DESCRIPTION:**

The IEC '**Pulley on Straight Rod**'. Uses a 50mm diameter, low mass, high strength nylon pulley, fitted to 8mm diameter rod for fitting to a bench clamp LB0858-001 or similar. MF2600-001 has a straight rod and model MF2600-020 has an offset rod to provide a lower profile pulley position when fitted to the bench clamp.

The IEC '**Bench Clamp**' (not supplied with the Pulley on Rod) fits a 40mm thick bench. This Universal Bench Clamp accepts from 5mm to 13mm diameter rods, both vertical and horizontal. It is a general purpose bench clamp for use in the laboratory for supporting retort rods, pulleys and similar apparatus.

**MF2600-001 pulley on straight rod**



**LB0858-001 bench clamp**

**purchase separately**



**Physical size: pulley on rod: 50x200mm DxL Weight: 0.03 kg**

**BENCH CLAMP:** This bench clamp LB0858-001 is specially designed to have multi-purpose use in the laboratory and also to provide great strength. It is designed to fit to thick benches and to accept up to 13mm diameter rods in either the vertical or horizontal planes for the support of other apparatus. The clamp itself can clamp to other rods to form strong frameworks. The clamp is complete with 2x 4mm diameter holes extruded through the thickness of the body to permit the very strong fixing to a flat surface like a board or a wall.

The unit is complete with large steel knurled head knobs and screws for strong clamping to both the bench and the rods. The bench clamping screw is fitted with a nylon tip protector.

When the '**Pulley on Offset Rod**' MF2600-020 is fitted to the clamp, the pulley can be brought down to a very low position for use with cords passing over the edge of benches.

The specially contoured rod receptacles can rigidly clamp rods down to 5mm diameter.

**Designed and manufactured in Australia**